



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A		
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Manager Global Product Compliance		
<b>Company Unique ID</b>	-	<b>Response Date</b>	2013-07-04	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5-104549-7	<b>Amount</b>	3108.055376	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>REACH-0209</b>	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	5-146875-2				3.0	24.681288	mg	
Material	2	Tin Plate				3.0	0.537418	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	3.0	5.3688E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	3.0	0.53688	mg	
Material	2	Beryllium Copper				3.0	23.8815	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	3.0	0.47763	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00238815	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.00238815	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	3.0	0.0047763	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.6	3.0	0.14329	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	2.3881E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	3.0	0.14329	mg	
Substance	3	Copper	Supplier	7440-50-8	96.0485	3.0	22.93782	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	1.1941E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	0.0238815	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.6	3.0	0.14329	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.00238815	mg	
Material	2	Nickel Plate				3.0	0.26237	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	3.0	5.2474E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	2.6237E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.26158	mg	
Sub-Item	1	146719-6				1.0	1858.3	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	1858.3	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	55.749	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	1245.061	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	557.49	mg	

Sub-Item	1	8-103917-2				50.0	23.51423024	mg	
Material	2	Phos Bronze				50.0	23.24	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	50.0	22.00445	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	50.0	0.004648	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	50.0	0.002324	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	50.0	1.0458	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	50.0	0.003486	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	50.0	0.02324	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	50.0	0.002324	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	50.0	2.324E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	50.0	0.06972	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	50.0	0.02324	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	50.0	0.02324	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	50.0	0.002324	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	50.0	0.01162	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	50.0	0.02324	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	50.0	1.162E-4	mg	
Material	2	Tin Plate				50.0	0.0746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	50.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	50.0	0.07452547	mg	
Material	2	Gold Plate				50.0	0.00243024	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.00242295	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	50.0	1.0E-5	mg	
Material	2	Gold Plate				50.0	0.0602	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.0600194	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	50.0	1.806E-4	mg	
Material	2	Nickel Plate				50.0	0.137	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	50.0	2.74E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	50.0	1.37E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	50.0	0.13659	mg	