



Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A							
Supplier Information														
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER							
Company Unique ID	-	Response Date	2013-05-02	Contact Email	cc.wu@te.com									
Contact Phone Number	(86)21-33259321													
Legal Statement														
Supplier Acceptance	true													
Legal Statement														
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.														
Product														
Manufacturer Item number	34160	Amount	1124.72155	Version	-	Identity								
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority								
Date		UOM	Each											
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions													
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products													
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH													
Product Disclosure														
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption					
Material	1	PVC				1.0	175.63658	mg						
Substance	2	Ethene, chloro-	Supplier	75-01-4	2.0E-4	1.0	3.5127E-4	mg						
Substance	2	Limestone	Supplier	1317-65-3	2.0	1.0	3.51273	mg						
Substance	2	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	1.5	1.0	2.63455	mg						
Substance	2	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.1	1.0	0.17564	mg						
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	8.3998	1.0	14.75312	mg						
Substance	2	Ethene, chloro-, homopolymer	Polyvinyl Chloride (PVC)	9002-86-2	88.0	1.0	154.56019	mg						
Material	1	Colorant				1.0	3.58442	mg						
Substance	2	Copper, [29H,31H-phthalocyaninato(2-)-.kappa.N29,.kappa.N30,.kappa.N31,.kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	5.5	1.0	0.19714	mg						
Substance	2	Rosin	Supplier	8050-09-7	0.0050	1.0	1.7922E-4	mg						
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	10.0	1.0	0.35844	mg						
Substance	2	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	0.5	1.0	0.0179221	mg						
Substance	2	Ethene, chloro-	Supplier	75-01-4	3.0E-4	1.0	1.075326E-5	mg						
Substance	2	Aluminate (Al(OH)63-), (OC-6-11)-, magnesium carbonate hydroxide (2:6:1:4)	Supplier	11097-59-9	1.0	1.0	0.0358442	mg						
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	0.5	1.0	0.0179221	mg						
Substance	2	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	0.0358442	mg						

Substance	2	2-Naphthalenecarboxylic acid, 4-[2-(5-chloro-4-methyl-2-sulphophenyl)diazenyl]-3-hydroxy-, calcium salt (1:1)	Supplier	7023-61-2	0.1	1.0	0.00358442	mg	
Substance	2	Limestone	Supplier	1317-65-3	1.0	1.0	0.0358442	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	8.0	1.0	0.28675	mg	
Substance	2	Ethene, homopolymer, oxidized	Supplier	68441-17-8	3.0	1.0	0.10753	mg	
Substance	2	Carbon black	Supplier	1333-86-4	0.5	1.0	0.0179221	mg	
Substance	2	Ethene, chloro-, homopolymer	Polyvinyl Chloride (PVC)	9002-86-2	68.8947	1.0	2.46948	mg	
Material	1	Copper				1.0	938.0	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.05	1.0	0.469	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00938	mg	
Substance	2	Copper	Supplier	7440-50-8	99.6975	1.0	935.16255	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00938	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0938	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.0938	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	0.1876	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	0.938	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.938	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00469	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0938	mg	
Material	1	Tin Plate				1.0	7.50055	mg	
Substance	2	Tin	Supplier	7440-31-5	99.5	1.0	7.46305	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.0300022	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00750055	mg	