



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer																											
Company Unique ID	1473	Response Date	2014-05-19	Contact Email	cc.wu@te.com																													
Contact Phone Number		021-33259321																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	350689-1	Amount	279.1365	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Manufacturing Information																																		
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info																												
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psl Rating Reflow																												
Max Time Within 5		Psl Rating Wave		Package Designator		Size	0.0																											
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	Brass																											
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	Tin (Sn)																											
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC																											
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	350570-1				1.0	279.1365	mg																										
Material	2	Tin Plate				1.0	2.4165	mg																										
Substance	3	Tin	Supplier	7440-31-5	97.85	1.0	2.36455	mg																										
Substance	3	Copper	Supplier	7440-50-8	1.5	1.0	0.0362475	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.35	1.0	0.00845775	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.2	1.0	0.004833	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0024165	mg																										
Material	2	Brass				1.0	276.72	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0027672	mg																										
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	77.54386	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.13836	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.027672	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.13836	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.27672	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0027672	mg																										
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	197.8548	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.027672	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0013836	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.55344	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.013836	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.13836	mg																										