



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Kiwi Lee	Contact Title	Senior Engineer Product Compliance																											
Company Unique ID	485203835	Response Date	2014-04-29	Contact Email	kiwi.lee@te.com																													
Contact Phone Number		886-2-87682788																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5-5179009-2	Amount	1266.85930482	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	2-1735149-2				1.0	810.0	mg																										
Material	2	LCP-GF30				1.0	810.0	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	243.0	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.4	1.0	3.24	mg																										
Substance	3	1,4-Benzenedicarb oxylic acid, polymer with [1,1-biphenyl]- 4,4-diol, 4- hydroxybenzoi c acid, 6- hydroxy-2- naphthalenecar boxylic acid and N-(4- hydroxyphenyl) acetamide	Supplier	147310-94-9	69.6	1.0	563.76	mg																										
Sub-Item	1	3-179013-2				60.0	7.61432175	mg																										
Material	2	Nickel Plate				60.0	0.498	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	60.0	9.96E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	60.0	4.98E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	60.0	0.49651	mg																										
Material	2	Tin Plate				60.0	0.113223	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	60.0	1.1311E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	60.0	0.11311	mg																										
Material	2	Beryllium Copper				60.0	7.0	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	60.0	7.0E-5	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	60.0	0.0014	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.2	60.0	0.014	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.2	60.0	0.014	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.5	60.0	0.035	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.6	60.0	0.042	mg																										
Substance	3	Copper	Supplier	7440-50-8	98.1035	60.0	6.86724	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	60.0	7.0E-4	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	60.0	7.0E-4	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.2	60.0	0.014	mg																										

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	60.0	3.5E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	60.0	3.5E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	60.0	0.0070	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	60.0	0.0035	mg	
Material	2	Gold Plate				60.0	0.00309875	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	60.0	0.00308945	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	60.0	1.0E-5	mg	