



| | | | | | | | | | |
|---|---|---|---------------------------|----------------------|--------------------------------|----------------------|----------------------|------------|------------------|
| Form Type | Distribute | Version | 2.0 | Sectionals | Material Info | Subsectionals | D, A | | |
| Supplier Information | | | | | | | | | |
| Company Name | TE Connectivity | Request Document ID | | Contact Name | Vincent M Pascucci | Contact Title | Compliance Engineer | | |
| Company Unique ID | - | Response Date | 2013-02-26 | Contact Email | vincent.pascucci@te.com | | | | |
| Contact Phone Number | 717-986-7822 | | | | | | | | |
| Legal Statement | | | | | | | | | |
| Supplier Acceptance | true | | | | | | | | |
| Legal Statement | | | | | | | | | |
| The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers. | | | | | | | | | |
| Product | | | | | | | | | |
| Manufacturer Item number | 5-534237-6 | Amount | 872.4844 | Version | - | Identity | | | |
| Manufacturer Item Name | | Weight Uom | mg | Mfr Site | | Authority | | | |
| Date | | UOM | Each | | | | | | |
| EUroHS-0508 | Product(s) meets EU RoHS requirement without any exemptions | | | | | | | | |
| ChinaRoHS-0508 | Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products | | | | | | | | |
| REACH-0209 | Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH | | | | | | | | |
| Product Disclosure | | | | | | | | | |
| Sub-Item/Material/Substance | Level | Name | Substance Category | Substance CAS | Substance Concentration | Quantity | Mass per Unit | UOM | Exemption |
| Sub-Item | 1 | 1571967-6 | | | | 1.0 | 638.31 | mg | |
| Material | 2 | PCT-GF30 | | | | 1.0 | 638.31 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0909 | 10.0 | 1.0 | 63.831 | mg | |
| Substance | 3 | Arsenic | Supplier | 7440-38-2 | 0.02 | 1.0 | 0.12766 | mg | |
| Substance | 3 | Talc (Mg3H2(SiO3)4) | Supplier | 14807-96-6 | 5.0 | 1.0 | 31.9155 | mg | |
| Substance | 3 | Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17) | Supplier | 1043-4-FR17 | 20.0 | 1.0 | 127.662 | mg | |
| Substance | 3 | Glass, oxide, chemicals | Supplier | 65997-17-3 | 30.0 | 1.0 | 191.493 | mg | |
| Substance | 3 | 1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedi methanol | Supplier | 25135-20-0 | 29.97 | 1.0 | 191.30151 | mg | |
| Substance | 3 | Antimonate (SbO31-), sodium (1:1) | Supplier | 15432-85-6 | 5.0 | 1.0 | 31.9155 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.01 | 1.0 | 0.063831 | mg | |
| Sub-Item | 1 | 1-1571593-2 | | | | 8.0 | 29.2718 | mg | |
| Material | 2 | Nickel Plate | | | | 8.0 | 2.713 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0909 | 0.2 | 8.0 | 0.005426 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.1 | 8.0 | 0.002713 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 99.7 | 8.0 | 2.70486 | mg | |
| Material | 2 | Phos Bronze | | | | 8.0 | 25.958 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 94.6835 | 8.0 | 24.57794 | mg | |
| Substance | 3 | Manganese | Supplier | 7439-96-5 | 0.02 | 8.0 | 0.0051916 | mg | |
| Substance | 3 | Chromium | Supplier | 7440-47-3 | 0.01 | 8.0 | 0.0025958 | mg | |
| Substance | 3 | Tin | Supplier | 7440-31-5 | 4.5 | 8.0 | 1.16811 | mg | |
| Substance | 3 | Arsenic | Supplier | 7440-38-2 | 0.015 | 8.0 | 0.0038937 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 8.0 | 0.0025958 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.1 | 8.0 | 0.025958 | mg | |

| | | | | | | | | | |
|-----------|---|--|---------------------------|---------------|---------|-----|-----------|----|--|
| Substance | 3 | Beryllium | Supplier | 7440-41-7 | 0.0010 | 8.0 | 2.5958E-4 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 0.3 | 8.0 | 0.077874 | mg | |
| Substance | 3 | Phosphorus | Supplier | 7723-14-0 | 0.1 | 8.0 | 0.025958 | mg | |
| Substance | 3 | Cobalt | Supplier | 7440-48-4 | 0.1 | 8.0 | 0.025958 | mg | |
| Substance | 3 | Cadmium | Cadmium/Cadmium Compounds | 7440-43-9 | 0.01 | 8.0 | 0.0025958 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.05 | 8.0 | 0.012979 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 0.1 | 8.0 | 0.025958 | mg | |
| Substance | 3 | Mercury | Mercury/Mercury Compounds | 7439-97-6 | 5.0E-4 | 8.0 | 1.2979E-4 | mg | |
| Material | 2 | Tin Plate | | | | 8.0 | 0.575 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.0999 | 8.0 | 5.7443E-4 | mg | |
| Substance | 3 | Tin | Supplier | 7440-31-5 | 99.9001 | 8.0 | 0.57443 | mg | |
| Material | 2 | Gold Plate | | | | 8.0 | 0.0258 | mg | |
| Substance | 3 | Gold | Supplier | 7440-57-5 | 99.7 | 8.0 | 0.0257226 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0909 | 0.3 | 8.0 | 7.74E-5 | mg | |