



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Craig Darrell W	Contact Title	Mgr. Product Sustaining Engineering																											
Company Unique ID	485203835	Response Date	2014-04-14	Contact Email	darrell.craig@te.com																													
Contact Phone Number		336-665-6619																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5-641337-3	Amount	81488.2	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	641337-3				100.0	814.882	mg																										
Material	2	Gold Plate				100.0	0.702	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	100.0	0.002106	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	100.0	0.69989	mg																										
Material	2	Nickel Plate				100.0	3.15	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	100.0	0.0063	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	100.0	0.00315	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	100.0	3.14055	mg																										
Material	2	Phos Bronze				100.0	121.8	mg																										
Substance	3	Copper	Supplier	7440-50-8	94.6835	100.0	115.3245	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	100.0	0.02436	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	100.0	0.01218	mg																										
Substance	3	Tin	Supplier	7440-31-5	4.5	100.0	5.481	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.015	100.0	0.01827	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	100.0	0.01218	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	100.0	0.1218	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	100.0	0.001218	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	100.0	0.3654	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	100.0	0.1218	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	100.0	0.1218	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	100.0	0.01218	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	100.0	0.0609	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	100.0	0.1218	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	100.0	6.09E-4	mg																										
Material	2	POLYCARBONATE				100.0	689.23	mg																										
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-	Supplier	80-05-7	0.01	100.0	0.068923	mg																										

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	1.0	100.0	6.8923	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	98.99	100.0	682.26878	mg	