



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Lee, Kiwi	Contact Title	Product Compliance Engineer																											
Company Unique ID	485203835	Response Date	2014-05-15	Contact Email	kiwi.lee@te.com																													
Contact Phone Number		886-2-87682788																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5-1437536-5	Amount	3353.108	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true																																	
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	6-1437506-3				28.0	62.861	mg																										
Material	2	Beryllium Copper				28.0	27.0	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	28.0	0.0054	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	28.0	0.0027	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.4	28.0	0.108	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	2.0	28.0	0.54	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.2	28.0	0.054	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	28.0	0.0027	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.2	28.0	0.054	mg																										
Substance	3	Copper	Supplier	7440-50-8	96.1495	28.0	25.96036	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	28.0	2.7E-4	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.2	28.0	0.054	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0090	28.0	0.00243	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	28.0	0.054	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	28.0	1.35E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.6	28.0	0.162	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight																									
Material	2	Gold Plate				28.0	1.01	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	28.0	1.00697	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	28.0	0.00303	mg																										
Material	2	Copper				28.0	32.0	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	28.0	0.0032	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	28.0	0.0064	mg																										
Substance	3	Copper	Supplier	7440-50-8	99.6975	28.0	31.9032	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	28.0	3.2E-4	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	28.0	0.0032	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	28.0	3.2E-4	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	28.0	0.032	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	28.0	0.0032	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	28.0	1.6E-4	mg																										

Substance	3	Nickel	Nickel	7440-02-0	0.05	28.0	0.016	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	28.0	0.032	mg	
Material	2	Copper Plate				28.0	0.09	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	28.0	9.0E-5	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	28.0	0.08991	mg	
Material	2	Tin-Lead Plate				28.0	1.081	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	28.0	0.99776	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	28.0	0.007567	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	28.0	0.07567	mg	
Material	2	Nickel Plate				28.0	1.68	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	28.0	0.00336	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	28.0	0.00168	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	28.0	1.67496	mg	
Sub-Item	1	2-1437532-8				1.0	1593.0	mg	
Material	2	POLYESTER PCT				1.0	1593.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	9.75	1.0	155.3175	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	28.5	1.0	454.005	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.0	1.0	302.67	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedi methanol	Supplier	25135-20-0	33.25	1.0	529.6725	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	9.5	1.0	151.335	mg	