



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A
<b>Supplier Information</b>									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Mgr Environmental Engineering		
Company Unique ID	-	Response Date	2014-05-27	Contact Email	jrpenica@te.com				
Contact Phone Number	7175923266								
<b>Legal Statement</b>									
Supplier Acceptance	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
Manufacturer Item number	350783-1	Amount	11517.7	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-0613	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true								
<b>Manufacturing Information</b>									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
<b>Product Disclosure</b>									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	705287-4				1.0	11517.7	mg	
Material	2	PA				1.0	11517.7	mg	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	37.57074	mg	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	53.40757	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	0.0345531	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	0.9451	1.0	108.85378	mg	
Substance	3	Benzenepropynamide, N,N-1,6-hexanediybis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	46.11687	mg	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	0.38008	mg	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	2.87942	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	23.17361	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediybis-	Supplier	110-30-5	0.1901	1.0	21.89515	mg	

Substance	3	1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	1044.85119	mg	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	10178.53702	mg	