



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	M. Global Product Compliance																											
Company Unique ID	485203835	Response Date	2014-09-12	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	382575-2	Amount	62.024	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	382583-1				0.1	570.0	mg																										
Material	2	PBT-GF30FR(17)				0.1	570.0	mg																										
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	0.1	171.0	mg																										
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	0.1	188.1	mg																										
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	0.1	5.7	mg																										
Substance	3	Carbon black	Supplier	1333-86-4	1.0	0.1	5.7	mg																										
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	0.1	28.5	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	0.1	171.0	mg																										
Sub-Item	1	382582-1				1.0	5.024	mg																										
Material	2	Beryllium Copper				1.0	5.0	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	2.0	1.0	0.1	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	5.0E-4	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0010	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.2	1.0	0.01	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.2	1.0	0.01	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.4	1.0	0.02	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	5.0E-4	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.2	1.0	0.01	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	5.0E-5	mg																										
Substance	3	Copper	Supplier	7440-50-8	96.649	1.0	4.83245	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0050	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.01	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	2.5E-4	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.5E-5	mg																										
Material	2	Gold Plate				1.0	0.0094	mg																										

Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.0093718	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	2.82E-5	mg	
Material	2	Nickel Plate				1.0	0.0146	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	2.92E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.46E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.0145562	mg	