



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	485203835	Response Date	2013-09-23	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	530153-2	Amount	313.11575	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	2-530154-2				0.0	79.551	mg	
Material	2	Unspecified Compliant Material				0.0	3.18204	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	100.0	0.0	3.18204	mg	
Material	2	PBT				0.0	76.36896	mg	
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	0.0	0.15274	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	0.0	3.81845	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	0.0	0.07636896	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	0.0	6.10952	mg	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	0.0	0.07636896	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	0.0	0.38184	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	0.0	0.07636896	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	0.0	0.38184	mg	

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	0.0	22.91069	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	0.0	3.81845	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	0.0	1.52738	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	0.0	0.07636896	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	0.0	36.96258	mg	
Sub-Item	1	530155-2				2.0	146.614	mg	
Material	2	Gold Plate				2.0	0.361	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.1	2.0	3.61E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.9	2.0	0.36064	mg	
Material	2	Nickel Plate				2.0	0.546	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	5.46E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.54436	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	2.0	0.001092	mg	
Material	2	Phos Bronze				2.0	145.707	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0291414	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1335	2.0	135.70203	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	2.0	0.43712	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.0145707	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	2.0	0.50997	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.14571	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	2.0	0.02185605	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00145707	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.14571	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0145707	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	2.0	8.45101	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.0145707	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	7.2853E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.0728535	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.14571	mg	