



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer		
Company Unique ID	1473	Response Date	2014-06-19	Contact Email	cc.wu@te.com				
Contact Phone Number	021-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	53884-3	Amount	6.69842	Version	-	Identity			
Manufacturer Item Name		Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-0613	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true								
Manufacturing Information									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		PSI Rating Reflow			
Max Time Within 5		PSI Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	53881-3				1.0	5.54	g	
Material	2	PC				1.0	5.54	g	
Substance	3	Carbon black	Supplier	1333-86-4	0.5	1.0	0.0277	g	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-	Supplier	80-05-7	0.01	1.0	5.54E-4	g	
Substance	3	Phenol, 2,4-bis(1,1-dimethylethyl)-, 1,1,1-phosphite	Supplier	31570-04-4	0.15	1.0	0.00831	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	95.34	1.0	5.281836	g	
Substance	3	Benzenesulfonic acid, 3-(phenylsulfonyl)-, potassium salt (1:1)	Supplier	63316-43-8	0.5	1.0	0.0277	g	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[(1-oxooctadecyl)oxy]methyl]-1,3-propanediyl ester	Supplier	115-83-3	0.5	1.0	0.0277	g	

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	3.0	1.0	0.1662	g	
Sub-Item	1	53882-3				1.0	1.15842	g	
Material	2	Stainless Steel				1.0	1.15842	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00115842	g	
Substance	3	Sulfur	Supplier	7704-34-9	0.015	1.0	1.7376E-4	g	
Substance	3	Silicon	Supplier	7440-21-3	0.5	1.0	0.0057921	g	
Substance	3	Copper	Supplier	7440-50-8	2.5	1.0	0.0289605	g	
Substance	3	Carbon	Supplier	7440-44-0	0.03	1.0	3.4753E-4	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	1.1584E-4	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.015	1.0	1.7376E-4	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.15842E-5	g	
Substance	3	Manganese	Supplier	7439-96-5	0.5	1.0	0.0057921	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.00115842	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	1.1584E-4	g	
Substance	3	Chromium	Supplier	7440-47-3	12.5	1.0	0.1448025	g	
Substance	3	Iron	Supplier	7439-89-6	72.3085	1.0	0.83763613	g	
Substance	3	Molybdenum	Supplier	7439-98-7	0.5	1.0	0.0057921	g	
Substance	3	Titanium	Supplier	7440-32-6	1.4	1.0	0.01621788	g	
Substance	3	Nickel	Nickel	7440-02-0	9.5	1.0	0.1100499	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	5.7921E-6	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	1.1584E-4	g	