



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2013-12-17	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	499141-3	Amount	5283.1215056	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	102142-9				1.0	3420.0	mg	
Material	2	PBT-GF30FR(17)				1.0	3420.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	1026.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	1128.6	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	171.0	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	34.2	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	34.2	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1026.0	mg	
Sub-Item	1	102132-3				8.0	52.2705941	mg	
Material	2	Tin-Lead Plate				8.0	0.26	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	8.0	0.0182	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	8.0	0.23998	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	8.0	0.00182	mg	
Material	2	Nickel Plate				8.0	0.92	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	8.0	0.00184	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	8.0	9.2E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	8.0	0.91724	mg	
Material	2	Gold Plate				8.0	0.113562	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	8.0	0.11322	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	8.0	3.4069E-4	mg	
Material	2	Brass				8.0	50.891	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	8.0	0.050891	mg	

Substance	3	Copper	Supplier	7440-50-8	64.0	8.0	32.57024	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	8.0	0.0254455	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	8.0	5.0891E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	8.0	0.0050891	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	8.0	0.050891	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	8.0	0.050891	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	8.0	17.91796	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	8.0	0.0050891	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	8.0	0.0050891	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	8.0	0.0254455	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	8.0	0.15267	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	8.0	0.0050891	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	8.0	2.5446E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	8.0	0.0254455	mg	
Material	2	Gold Plate				8.0	0.0860321	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	8.0	0.085774	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	8.0	2.581E-4	mg	
Sub-Item	1	102320-1				2.0	449.0	mg	
Material	2	PBT-GF30FR(17)				2.0	449.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	2.0	134.7	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	2.0	148.17	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	2.0	22.45	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	2.0	4.49	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	2.0	4.49	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	2.0	134.7	mg	
Sub-Item	1	102132-6				8.0	68.3695941	mg	
Material	2	Tin-Lead Plate				8.0	0.26	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	8.0	0.0182	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	8.0	0.23998	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	8.0	0.00182	mg	
Material	2	Nickel Plate				8.0	1.12	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	8.0	0.00224	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	8.0	0.00112	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	8.0	1.11664	mg	
Material	2	Gold Plate				8.0	0.113562	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	8.0	0.11322	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	8.0	3.4069E-4	mg	
Material	2	Brass				8.0	66.79	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	8.0	0.06679	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	8.0	42.7456	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	8.0	0.033395	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	8.0	6.679E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	8.0	0.006679	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	8.0	0.06679	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	8.0	0.06679	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	8.0	23.51576	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	8.0	0.006679	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	8.0	0.006679	mg	

Substance	3	Aluminum	Supplier	7429-90-5	0.05	8.0	0.033395	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	8.0	0.20037	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	8.0	0.006679	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	8.0	3.3395E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	8.0	0.033395	mg	
Material	2	Gold Plate				8.0	0.0860321	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	8.0	0.085774	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	8.0	2.581E-4	mg	