



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A		
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Cc Wu	<b>Contact Title</b>	PROD COMPLIANCE ENGINEER		
<b>Company Unique ID</b>	-	<b>Response Date</b>	2013-05-09	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	(86)21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5555165-1	<b>Amount</b>	2261.719686	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>REACH-0209</b>	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	1-555075-1				1.0	1947.2	mg	
Material	2	PBT-GF20				1.0	1947.2	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	50.0	1.0	973.6	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	97.36	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	5.0	1.0	97.36	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	389.44	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromophenyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	20.0	1.0	389.44	mg	
Sub-Item	1	1-557500-6				1.0	314.519686	mg	
Material	2	Tin Plate				1.0	2.03	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00202797	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	2.02797	mg	
Material	2	Gold Plate				1.0	0.069686	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	2.0906E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.06947694	mg	
Material	2	Nickel Plate				1.0	2.24	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.00448	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00224	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.23328	mg	
Material	2	Phos Bronze				1.0	310.18	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.31018	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.031018	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.62036	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.046527	mg	

Substance	3	Copper	Supplier	7440-50-8	90.0335	1.0	279.26591	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.062036	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.08563	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0031018	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.31018	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.031018	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	27.9162	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.31018	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0015509	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.031018	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.15509	mg	