



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	485203835	Response Date	2013-10-07	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-103669-2	Amount	680.6949855	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	104906-2				1.0	528.0	mg	
Material	2	PCT-GF30				1.0	528.0	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	3.5	1.0	18.48	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	5.8	1.0	30.624	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	158.4	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedi methanol	Supplier	25135-20-0	46.7	1.0	246.576	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	14.0	1.0	73.92	mg	
Sub-Item	1	6-104841-4				3.0	50.8983285	mg	
Material	2	Tin Plate				3.0	1.0806	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	3.0	0.00107952	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	3.0	1.07952	mg	
Material	2	Brass				3.0	49.16	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	4.916E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0175	3.0	13.7734	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.02458	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.004916	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.02458	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.04916	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	35.1494	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	4.916E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.004916	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	2.458E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.09832	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.004916	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.02458	mg	
Material	2	Nickel Plate				3.0	0.6577285	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	3.0	0.00131546	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	6.5773E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.65576	mg	