



Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A		
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	-	Response Date	2013-05-09	Contact Email	cc.wu@te.com				
Contact Phone Number	(86)21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-103673-2	Amount	956.448	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1825484-2				1.0	793.953	mg	
Material	2	LCP-GF30				1.0	793.953	mg	
Substance	3	Carbon black	Supplier	1333-86-4	10.0	1.0	79.3953	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	1.0	1.0	7.93953	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	10.0	1.0	79.3953	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	40.0	1.0	317.5812	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	39.0	1.0	309.64167	mg	
Sub-Item	1	6-104841-7				3.0	54.165	mg	
Material	2	Nickel Plate				3.0	0.334	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	3.0	6.68E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	3.34E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.333	mg	
Material	2	Tin Plate				3.0	0.547	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	3.0	5.4645E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	3.0	0.54645	mg	
Material	2	Brass				3.0	53.2	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	5.32E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0175	3.0	14.90531	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.0266	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00532	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.0266	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.0532	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	38.038	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	5.32E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.00532	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	2.66E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.1064	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.00532	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.0266	mg	
Material	2	Gold Plate				3.0	0.084	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	3.0	0.083748	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	3.0	2.52E-4	mg	