



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	-	Response Date	2013-08-07	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5555980-1	Amount	2976.870077	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1-556588-3				1.0	2729.8	mg	
Material	2	PBT-GF20				1.0	2729.8	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	50.0	1.0	1364.9	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	136.49	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	5.0	1.0	136.49	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	545.96	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromophenyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	20.0	1.0	545.96	mg	
Sub-Item	1	1-556549-3				1.0	247.070077	mg	
Material	2	Gold Plate				1.0	1.755055	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.00526517	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	1.74979	mg	
Material	2	Nickel Plate				1.0	0.892571	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.00178514	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	8.9257E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.88989	mg	
Material	2	Phos Bronze				1.0	244.4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.2444	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.02444	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.4888	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.03666	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0335	1.0	220.04187	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.04888	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	0.8554	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.002444	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.2444	mg	

Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.02444	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	21.996	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.2444	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.001222	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.02444	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.1222	mg	
Material	2	Tin Plate				1.0	0.022451	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	2.242855E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.02242857	mg	