



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	485203835	Response Date	2014-08-21	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-104078-3	Amount	1082.119644	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	2-104002-4				1.0	319.710644	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	319.710644	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	9.59132	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	214.20613	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	95.91319	mg	
Sub-Item	1	5-146101-2				10.0	76.2409	mg	
Material	2	Nickel Plate				10.0	0.6899	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	0.0013798	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	6.899E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.68783	mg	
Material	2	Tin Plate				10.0	0.1666	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	10.0	1.6643E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	10.0	0.16643	mg	
Material	2	Phos Bronze				10.0	74.8424	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	10.0	70.8634	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	0.01496848	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.00748424	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	10.0	3.36791	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	10.0	0.01122636	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.00748424	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	0.0748424	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	7.4842E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	0.22453	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	10.0	0.0748424	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.0748424	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.00748424	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.0374212	mg	

Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	0.0748424	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	3.7421E-4	mg	
Material	2	Gold Plate				10.0	0.542	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.54037	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	0.001626	mg	