



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Kim, Seong Kyung	Contact Title	Account Manager		
Company Unique ID	TE Connectivity	Response Date	2014-10-28	Contact Email	sophie.kim@te.com				
Contact Phone Number	82-2-3415-4614								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5556416-1	Amount	2863.8629147	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1-557535-6				1.0	303.8729147	mg	
Material	2	Phos Bronze				1.0	301.37	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.30137	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.030137	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.60274	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.0452055	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0335	1.0	271.33396	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.0548	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.060274	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0030137	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.030137	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.30137	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	27.1233	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.30137	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00150685	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.030137	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.15069	mg	
Material	2	Tin Plate				1.0	0.31	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	3.0969E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.30969	mg	
Material	2	Nickel Plate				1.0	2.1	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0021	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0042	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.0937	mg	
Material	2	Gold Plate				1.0	0.0929147	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	2.7874E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.09263596	mg	
Sub-Item	1	1-520255-2				1.0	2559.99	mg	
Material	2	PBT-GF20-FR(17)				1.0	2559.99	mg	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	2.55999	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	7.67997	mg	
Substance	3	Phosphoric acid, zinc salt (2:1)	Supplier	13598-37-3	1.0	1.0	25.5999	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	51.1998	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	20.0	1.0	511.998	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	511.998	mg	
Substance	3	Any substance originating from animal tissues of bovine, ovine, caprine, deer, elk, mink and cats species	Supplier	TE-Animal byproduct	1.0	1.0	25.5999	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	255.999	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	44.6	1.0	1141.75554	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	25.5999	mg	