



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2013-12-19	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5745077-4	Amount	6220.7724642	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s) - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	747889-4				2.0	670.4033	mg	
Material	2	Brass				2.0	666.2	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.006662	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.06662	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.6662	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.06662	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.13324	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.006662	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	2.0	2.3317	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	2.0	218.16384	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	2.0	419.706	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.003331	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.06662	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	2.0	24.6494	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.3331	mg	
Material	2	Nickel Plate				2.0	3.94	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	2.0	0.00788	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00394	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	3.92818	mg	
Material	2	Copper Plate				2.0	0.2633	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	2.633E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	2.0	0.26304	mg	
Sub-Item	1	7-66685-2				15.0	67.19772428	mg	
Material	2	Phos Bronze				15.0	65.7	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	15.0	62.20706	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	15.0	0.01314	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	15.0	0.00657	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	15.0	2.9565	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	15.0	0.009855	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	15.0	0.0657	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	15.0	0.00657	mg	

Substance	3	Beryllium	Supplier	7440-41-7	0.0010	15.0	6.57E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	15.0	0.1971	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	15.0	0.0657	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	15.0	0.0657	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	15.0	0.00657	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	15.0	0.03285	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	15.0	0.0657	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	15.0	3.285E-4	mg	
Material	2	Nickel Plate				15.0	1.07925	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	15.0	0.0021585	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	15.0	0.00107925	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	15.0	1.07601	mg	
Material	2	Gold Plate				15.0	0.00280028	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	15.0	0.00279188	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	15.0	1.0E-5	mg	
Material	2	Tin Plate				15.0	0.37503	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	15.0	3.7465E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	15.0	0.37466	mg	
Material	2	Gold Plate				15.0	0.040644	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	15.0	0.04052207	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	15.0	1.2193E-4	mg	
Sub-Item	1	207320-3				1.0	3872.0	mg	
Material	2	PBT-GF30FR(17)				1.0	3872.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	1161.6	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	1277.76	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	193.6	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	38.72	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	38.72	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1161.6	mg	