



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Mgr. Global Product Compliance		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2014-09-27	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5-104652-5	<b>Amount</b>	1085.7	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>EUREACH-1213</b>	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	5-104783-2				2.0	29.255	mg	
Material	2	Tin Plate				2.0	0.384	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	2.0	0.38208	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	2.0	0.001536	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	3.84E-4	mg	
Material	2	Nickel Plate				2.0	0.234	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	4.68E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	2.34E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.2333	mg	
Material	2	Beryllium Copper				2.0	28.637	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	2.0	0.57274	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0028637	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0057274	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.2	2.0	0.057274	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.2	2.0	0.057274	mg	
Substance	3	Iron	Supplier	7439-89-6	0.4	2.0	0.11455	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0028637	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	0.057274	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	2.8637E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	96.649	2.0	27.67737	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.028637	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.057274	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00143185	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.4318E-4	mg	
Sub-Item	1	104794-5				1.0	401.0	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	401.0	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	12.03	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	268.67	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	120.3	mg	
Sub-Item	1	5-104653-2				50.0	12.5238	mg	
Material	2	Gold Plate				50.0	0.0518	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.0516446	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	50.0	1.554E-4	mg	
Material	2	Nickel Plate				50.0	0.066	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	50.0	1.32E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	50.0	6.6E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	50.0	0.065802	mg	
Material	2	Copper Alloy				50.0	12.336	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	50.0	0.006168	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.0	50.0	0.12336	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.2	50.0	0.14803	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	50.0	0.012336	mg	
Substance	3	Copper	Supplier	7440-50-8	92.7635	50.0	11.44331	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	50.0	0.0074016	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	50.0	1.2336E-4	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.3	50.0	0.037008	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	50.0	0.012336	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	50.0	0.024672	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	50.0	0.0012336	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	50.0	0.0012336	mg	
Substance	3	Nickel	Nickel	7440-02-0	4.2	50.0	0.51811	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	50.0	6.168E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	50.0	6.168E-5	mg	
Material	2	Tin Plate				50.0	0.07	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	50.0	6.993E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	50.0	0.06993007	mg	