



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-01-15	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5745082-1	Amount	15316.82592	Version	-	Identity			
Manufacturer Item Name	STRAIN RELIEF ASSY KIT	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MOUNTING SCREW,ZINC PLTD				2.0	550.3372	mg	
Material	2	Carbon Steel				2.0	530.0	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	2.0	0.212	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.053	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	2.0	520.71705	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.053	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.53	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	2.0	0.265	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.0053	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.23	2.0	1.219	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	2.0	0.795	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	2.0	5.3	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.053	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.00265	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.53	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.265	mg	
Material	2	Tri Chrome Film				2.0	0.0394	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.02364	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	2.0	0.00394	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.01182	mg	
Material	2	Zinc Plate				2.0	20.2978	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	2.0	20.2978	mg	
Sub-Item	1	HOUSING HALF				2.0	6163.177	mg	
Material	2	FOAMING AGENT-701035L				2.0	61.63177	mg	
Substance	3	Octadecanoic acid	Supplier	57-11-4	0.05	2.0	0.03081588	mg	

Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-(1-oxooctadecyl)-.omega.-[(1-oxooctadecyl)oxy]-	Supplier	9005-08-7	0.65	2.0	0.40061	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-hydro-.omega.-hydroxy-	Supplier	25322-68-3	0.05	2.0	0.03081588	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-(1-oxooctadecyl)-.omega.-hydroxy-	Supplier	9004-99-3	0.25	2.0	0.15408	mg	
Substance	3	Diazene-1,2-dicarboxamide (C,C-azodi(formamide))	Supplier	123-77-3	10.0	2.0	6.16318	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	88.0	2.0	54.23596	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	1.0	2.0	0.61632	mg	
Material	2	POLYPROPYLENE				2.0	6101.54523	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	0.2999	2.0	18.29853	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	99.7001	2.0	6083.2467	mg	
Sub-Item	1	SCREW, MACHINE, FILLISTER HEAD, SLOT				2.0	754.24	mg	
Material	2	Carbon Steel				2.0	724.0	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	2.0	0.2896	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0724	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	2.0	711.31914	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0724	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.724	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	2.0	0.362	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00724	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.23	2.0	1.6652	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	2.0	1.086	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	2.0	7.24	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.0724	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.00362	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.724	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.362	mg	
Material	2	Tri Chrome Film				2.0	0.04	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.024	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	2.0	0.0040	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.012	mg	
Material	2	Zinc Plate				2.0	30.2	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	2.0	30.2	mg	
Sub-Item	1	NUT, 4-40, PLATED				2.0	190.65876	mg	
Material	2	Tri Chrome Film				2.0	0.00876	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.002628	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	2.0	8.76E-4	mg	

Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.005256	mg	
Material	2	Carbon Steel				2.0	189.0	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.2	2.0	0.378	mg	
Substance	3	Iron	Supplier	7439-89-6	97.5175	2.0	184.30807	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.00189	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.4	2.0	0.756	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.3	2.0	0.567	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.3	2.0	2.457	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0189	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0189	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.189	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00189	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	9.45E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.0189	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.189	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.0945	mg	
Material	2	Zinc Plate				2.0	1.65	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	2.0	1.65	mg	