



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A
<b>Supplier Information</b>									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer		
Company Unique ID	1473	Response Date	2014-05-08	Contact Email	cc.wu@te.com				
Contact Phone Number	021-33259321								
<b>Legal Statement</b>									
Supplier Acceptance	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
Manufacturer Item number	5-104666-3	Amount	2.39916921	Version	-	Identity			
Manufacturer Item Name		Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Manufacturing Information</b>									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
<b>Product Disclosure</b>									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	8-103917-2				40.0	0.02351423	g	
Material	2	Gold Plate				40.0	2.43024E-6	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	1.0E-8	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	2.422949E-6	g	
Material	2	Nickel Plate				40.0	1.37E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	2.74E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	1.37E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	1.3659E-4	g	
Material	2	Phos Bronze				40.0	0.02324	g	
Substance	3	Copper	Supplier	7440-50-8	94.6835	40.0	0.02200445	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	40.0	4.648E-6	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	40.0	2.324E-6	g	
Substance	3	Tin	Supplier	7440-31-5	4.5	40.0	0.0010458	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	40.0	3.486E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	2.324E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	40.0	2.324E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	40.0	2.324E-7	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	40.0	6.972E-5	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	40.0	2.324E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	40.0	2.324E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	40.0	2.324E-6	g	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	1.162E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	40.0	2.324E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	1.162E-7	g	
Material	2	Tin Plate				40.0	7.46E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	40.0	7.45254E-8	g	
Substance	3	Tin	Supplier	7440-31-5	99.9001	40.0	7.452547E-5	g	
Material	2	Gold Plate				40.0	6.02E-5	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	6.00194E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	40.0	1.806E-7	g	
Sub-Item	1	1-104034-7				1.0	1.4586	g	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	1.4586	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	0.043758	g	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	0.977262	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.43758	g	