



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2014-04-16	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5747838-4	Amount	12950.5156976	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	5749017-1				2.0	289.0	mg	
Material	2	Zinc Alloy				2.0	289.0	mg	
Substance	3	Iron	Supplier	7439-89-6	0.08	2.0	0.2312	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	2.0	0.10115	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0289	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00289	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0020	2.0	0.00578	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	2.0	0.1445	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	2.0	0.0578	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	2.0	0.289	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.289	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.1445	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0289	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.2145	2.0	275.1699	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	2.0	12.427	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	2.0	0.0578	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0030	2.0	0.00867	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.001445	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0040	2.0	0.01156	mg	
Sub-Item	1	745798-2				1.0	537.0	mg	
Material	2	PA46-GF30				1.0	537.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.5	1.0	29.535	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.6	1.0	8.592	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.5	1.0	104.715	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0060	1.0	0.03222	mg	
Substance	3	Hexanedioic acid, polymer with 1,4-butanediamine	Supplier	50327-77-0	43.386	1.0	232.98282	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	161.1	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0080	1.0	0.04296	mg	

Sub-Item	1	2-787661-8				12.0	101.4	mg	
Material	2	Phos Bronze				12.0	101.4	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	12.0	96.00907	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	12.0	0.02028	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	12.0	0.01014	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	12.0	4.563	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	12.0	0.01521	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	12.0	0.01014	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	12.0	0.1014	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	12.0	0.001014	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	12.0	0.3042	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	12.0	0.1014	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	12.0	0.1014	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	12.0	0.01014	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	12.0	0.0507	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	12.0	0.1014	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	12.0	5.07E-4	mg	
Sub-Item	1	748663-5				2.0	127.7	mg	
Material	2	Brass				2.0	127.7	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.001277	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	35.78473	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.06385	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.01277	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.06385	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.1277	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.001277	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	91.3055	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.01277	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	6.385E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.2554	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.006385	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.06385	mg	
Sub-Item	1	747331-3				2.0	154.74	mg	
Material	2	Brass				2.0	148.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.00148	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	41.4733	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.074	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0148	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.074	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.148	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00148	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	105.82	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0148	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	7.4E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.296	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.0074	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.074	mg	
Material	2	Tin Plate				2.0	3.03	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	2.0	0.01212	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	2.0	3.01485	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00303	mg	
Material	2	Copper Plate				2.0	3.71	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00371	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	2.0	3.70629	mg	
Sub-Item	1	2-787661-9				13.0	118.5869102	mg	
Material	2	Gold Plate				13.0	0.0263473	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	7.90419E-5	mg	

Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.02626826	mg	
Material	2	Gold Plate				13.0	0.0654919	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.06529542	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	13.0	1.9648E-4	mg	
Material	2	Nickel Plate				13.0	2.658	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.005316	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	0.002658	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	2.65003	mg	
Material	2	Tin Plate				13.0	0.337071	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	13.0	3.3673E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	13.0	0.33673	mg	
Material	2	Phos Bronze				13.0	115.5	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9999	13.0	109.35944	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	13.0	0.0231	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	13.0	0.01155	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	13.0	5.1975	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	13.0	0.017325	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.01155	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	13.0	0.1155	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	0.001155	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	13.0	0.3465	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	13.0	0.1155	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.1155	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	13.0	0.01155	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.05775	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	13.0	0.1155	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	5.775E-4	mg	
Sub-Item	1	1-745993-3				1.0	5365.6	mg	
Material	2	PA66-GF25				1.0	5365.6	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	214.624	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	321.936	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	187.796	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	61.5	1.0	3299.844	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	1341.4	mg	
Sub-Item	1	749743-8				1.0	3146.605865	mg	
Material	2	Tin Plate				1.0	51.631729	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.20653	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	51.37357	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.05163173	mg	
Material	2	Carbon Steel				1.0	3063.5	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	2.4508	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.6127	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.6127	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.30635	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.6127	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	4.59525	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.0635	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.30635	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	22.97625	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	12.254	mg	

Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	3.0635	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.030635	mg	
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	3007.69835	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.53175	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.30635	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0153175	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.0635	mg	
Material	2	Copper Plate				1.0	31.474136	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.03147414	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	31.44266	mg	