



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Darrell W Craig	Contact Title	MGR PROD SUSTAINING ENGINEERING		
Company Unique ID	485203835	Response Date	2014-03-01	Contact Email	darrell.craig@te.com				
Contact Phone Number	1-336-665-6619								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-555177-3	Amount	1205.652	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	555177-1				1.0	1205.652	mg	
Material	2	Nickel Plate				1.0	3.15	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.0063	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00315	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	3.14055	mg	
Material	2	Gold Plate				1.0	0.702	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.002106	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.69989	mg	
Material	2	Phos Bronze				1.0	121.8	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	115.3245	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.02436	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.01218	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	5.481	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.01827	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.1218	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.01218	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.001218	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.3654	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.1218	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.1218	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.01218	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0609	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.1218	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	6.09E-4	mg	
Material	2	POLYCARBONATE				1.0	1080.0	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-	Supplier	80-05-7	0.01	1.0	0.108	mg	

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	1.0	1.0	10.8	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	98.99	1.0	1069.092	mg	