



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Mgr. Global Product Compliance		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2013-12-04	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5-557315-3	<b>Amount</b>	1816.24	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	556441-1				1.0	1570.0	mg	
Material	2	POLYCARBONATE				1.0	1570.0	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-	Supplier	80-05-7	0.01	1.0	0.157	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	1.0	1.0	15.7	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	98.99	1.0	1554.143	mg	
Sub-Item	1	1933971-5				8.0	30.78	mg	
Material	2	Gold Plate				8.0	0.39	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	8.0	0.00117	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	8.0	0.38883	mg	
Material	2	Phos Bronze				8.0	29.99	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	8.0	28.39558	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	8.0	0.005998	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	8.0	0.002999	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	8.0	1.34955	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	8.0	0.0044985	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	8.0	0.02999	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	8.0	0.002999	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	8.0	2.999E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	8.0	0.08997	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	8.0	0.02999	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	8.0	0.02999	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	8.0	0.002999	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	8.0	0.014995	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	8.0	0.02999	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	8.0	1.4995E-4	mg	
Material	2	Nickel Plate				8.0	0.4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	8.0	8.0E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	8.0	4.0E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	8.0	0.3988	mg	