



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Prod Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-02-05	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5767096-8	<b>Amount</b>	1386.45365822	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	MICT,REC,038,ASY,,025,TAPE,CAP	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1213</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	38 POS. MICTOR RECEPTACLE HOUS				1.0	916.0	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	916.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	27.48	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	613.72	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	274.8	mg	
Sub-Item	1	VACUUM P/U CAP,REC LOOSE PIECE				1.0	111.4	mg	
Material	2	Aluminum Alloy				1.0	111.4	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	1.0	0.1114	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.05	1.0	0.0557	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.35	1.0	0.3899	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.05	1.0	0.0557	mg	
Substance	3	Iron	Supplier	7439-89-6	0.4	1.0	0.4456	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.25	1.0	0.2785	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.05	1.0	0.0557	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.05	1.0	0.0557	mg	
Substance	3	Aluminum	Supplier	7429-90-5	95.5945	1.0	106.49227	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	1.0	0.1114	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.1	1.0	0.1114	mg	
Substance	3	Magnesium	Supplier	7439-95-4	2.8	1.0	3.1192	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.0557	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	5.57E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0557	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00557	mg	
Sub-Item	1	LF MICTOR RECEPTACLE SIGNAL CO				38.0	7.90689454	mg	
Material	2	Tin Plate				38.0	0.00946137	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	38.0	1.0E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	38.0	0.00945192	mg	
Material	2	Copper Alloy				38.0	7.66	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	38.0	0.00383	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.0	38.0	0.0766	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.2	38.0	0.09192	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	38.0	0.00766	mg	
Substance	3	Copper	Supplier	7440-50-8	92.7635	38.0	7.10568	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	38.0	0.004596	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	38.0	7.66E-5	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.3	38.0	0.02298	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	38.0	0.00766	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	38.0	0.01532	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	38.0	7.66E-4	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	38.0	7.66E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	4.2	38.0	0.32172	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	38.0	3.83E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	38.0	3.83E-5	mg	
Material	2	Nickel Plate				38.0	0.23	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	38.0	4.6E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	38.0	2.3E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	38.0	0.22931	mg	
Material	2	Gold Plate				38.0	0.00743317	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	38.0	0.00741087	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	38.0	2.229951E-5	mg	
Sub-Item	1	MICTOR RECEPTACLE GROUND BUS CONTACT				1.0	58.5916657	mg	
Material	2	Tin Plate				1.0	0.0601836	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	6.012342E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.06012348	mg	
Material	2	Phos Bronze				1.0	56.58	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	53.57192	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.011316	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.005658	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	2.5461	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.008487	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.005658	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.05658	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.658E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.16974	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.05658	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.05658	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.005658	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.02829	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.05658	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.829E-4	mg	
Material	2	Nickel Plate				1.0	1.9	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0038	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0019	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	1.8943	mg	
Material	2	Gold Plate				1.0	0.0514821	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.05132765	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	1.5445E-4	mg	