



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2014-08-13	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5104338-1	Amount	1358.51922	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	111802-1				1.0	1199.0	mg	
Material	2	PPA-GF33				1.0	1199.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	1.5	1.0	17.985	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	4.0	1.0	47.96	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	33.0	1.0	395.67	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	11.99	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	23.0	1.0	275.77	mg	
Substance	3	1,3-Benzenedicarb oxlyic acid, polymer with 1,4-benzenedicarb oxlyic acid, 1,6-hexanediamine and hexanedioic acid	Supplier	27135-32-6	37.5	1.0	449.625	mg	
Sub-Item	1	2-1888096-2				10.0	15.951922	mg	
Material	2	Palladium-Nickel Plate				10.0	0.184642	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	10.0	0.14771	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	10.0	0.0369284	mg	
Material	2	Gold Plate				10.0	0.02361	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.02353917	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	7.083E-5	mg	
Material	2	Nickel Plate				10.0	0.52907	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	0.00105814	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	5.2907E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.52748	mg	

Material	2	Tin Plate				10.0	0.0246	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	10.0	2.45754E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	10.0	0.02457542	mg	
Material	2	Brass Wire				10.0	15.19	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	10.0	0.010633	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	10.0	10.86085	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	1.519E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	10.0	4.25282	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	10.0	0.007595	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	10.0	1.519E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	10.0	0.007595	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.01519	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	10.0	0.001519	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.001519	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.001519	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	7.595E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	10.0	0.03038	mg	