



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer		
Company Unique ID	485203835	Response Date	2014-03-25	Contact Email	cc.wu@te.com				
Contact Phone Number	+86-21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	640389-6	Amount	2554.871779	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Polyester Resin				1.0	1085.8	mg	
Material	2	PBT-GF7				1.0	1085.8	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis-	Supplier	80-05-7	0.01	1.0	0.10858	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	6.5	1.0	70.577	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	325.74	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	86.864	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	10.858	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.49	1.0	591.65242	mg	
Sub-Item	1	702429-9				1.0	1469.071779	mg	
Material	2	Nickel Plate				1.0	6.656787	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.01331357	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00665679	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	6.63682	mg	
Material	2	Brass				1.0	1451.50722	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	1037.82766	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01451507	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	1.0	406.38573	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.72575	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.01451507	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.72575	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.45151	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.14515	mg	

Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.14515	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	1.01606	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.14515	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00725754	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	2.90301	mg	
Material	2	Tin Plate				1.0	10.907772	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.01089686	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	10.89688	mg	