



Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A																
Supplier Information																							
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Manager Global Product Compliance																
Company Unique ID	-	Response Date	2013-02-22	Contact Email	jrpenica@te.com																		
Contact Phone Number		717-592-3266																					
Legal Statement																							
Supplier Acceptance	true																						
Legal Statement																							
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																							
Product																							
Manufacturer Item number	51864-2	Amount	938.656477	Version	-	Identity																	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																	
Date		UOM	Each																				
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																						
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH																						
Product Disclosure																							
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Mass	UOM	Exemption															
Sub-Item	1	51872-5				584.571477	mg																
Material	2	Tin Plate				6.244477	mg																
Substance	3	Tin	Supplier	7440-31-5	99.5	6.21325	mg																
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	0.02497791	mg																
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	0.00624448	mg																
Material	2	Copper				578.327	mg																
Substance	3	Nickel	Nickel	7440-02-0	0.05	0.28916	mg																
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	0.57833	mg																
Substance	3	Chromium	Supplier	7440-47-3	0.0010	0.00578327	mg																
Substance	3	Copper	Supplier	7440-50-8	99.6975	576.57756	mg																
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	0.00578327	mg																
Substance	3	Antimony	Supplier	7440-36-0	0.01	0.0578327	mg																
Substance	3	Arsenic	Supplier	7440-38-2	0.01	0.0578327	mg																
Substance	3	Manganese	Supplier	7439-96-5	0.02	0.11567	mg																
Substance	3	Cobalt	Supplier	7440-48-4	0.1	0.57833	mg																
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	0.00289164	mg																
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	0.0578327	mg																
Sub-Item	1	21958-1				354.085	mg																
Material	2	Tin Plate				5.0	mg																
Substance	3	Tin	Supplier	7440-31-5	99.5	4.975	mg																
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	0.02	mg																
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	0.0050	mg																
Material	2	PA66				45.57882	mg																
Substance	3	Copper	Supplier	7440-50-8	0.02	0.00911576	mg																
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.1	0.50137	mg																
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	98.78	45.02276	mg																
Substance	3	Bromine	Supplier	7726-95-6	0.1	0.04557882	mg																
Material	2	COLORANT				0.93018	mg																

Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.32	0.00297658	mg	
Substance	3	3H-Naphtho[1,2,3-de]quinoline-2,7-dione, 3-methyl-6-[(4-methylphenyl)amino]-	Supplier	81-39-0	0.1	9.3018E-4	mg	
Substance	3	Octadecanamide, N,N'-1,2-ethanediylobis-	Supplier	110-30-5	0.0090	8.37162E-5	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediylo)imino-1,6-hexanediylo]	Supplier	32131-17-2	98.98	0.92069	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.0010	1.0E-5	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.17	0.00158131	mg	
Substance	3	Copper, [29H,31H-phthalocyaninato (2-)-.kappa.N29,.kappa.N30,.kappa.N31,.kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	0.42	0.00390676	mg	
Material	2	Copper				302.576	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	0.15129	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	0.30258	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	0.00302576	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	301.66071	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	0.00302576	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	0.0302576	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	0.0302576	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	0.0605152	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	0.30258	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	0.00151288	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	0.0302576	mg	