



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2014-05-06	Contact Email	cc.wu@te.com				
Contact Phone Number	(86)21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	640442-4	Amount	690.524	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	640439-2				4.0	92.706	mg	
Material	2	Tin-Lead Plate				4.0	2.306	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	4.0	0.016142	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	4.0	2.12844	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	4.0	0.16142	mg	11 Lead used in compliant pin connector systems
Material	2	Phos Bronze				4.0	90.4	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1335	4.0	84.19268	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	0.01808	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	4.0	0.2712	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	4.0	0.00904	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	4.0	0.3164	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	4.0	0.01356	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	4.0	0.0904	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	9.04E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.0904	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.00904	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	4.0	5.2432	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	4.52E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	4.0	0.00904	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.0452	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	4.0	0.0904	mg	
Sub-Item	1	640538-4				1.0	319.7	mg	
Material	2	COLORANT				1.0	6.394	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	14.76	1.0	0.94375	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	1.0	1.0	0.06394	mg	
Substance	3	Poly[[imino(1-oxo-1,6-hexanedyl)]]	Supplier	25038-54-4	84.24	1.0	5.38631	mg	
Material	2	PA66				1.0	313.306	mg	

Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	99.0	1.0	310.17294	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	3.13306	mg	