



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	-	Response Date	2013-08-12	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5188835-1	Amount	8018.3219392	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1645361-6				44.0	30.6643168	mg	
Material	2	Nickel Plate				44.0	0.29	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	44.0	5.8E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	44.0	2.9E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	44.0	0.28913	mg	
Material	2	Palladium-Nickel Plate				44.0	0.021598	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	44.0	0.0172784	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	44.0	0.0043196	mg	
Material	2	Gold Plate				44.0	0.0124415	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	44.0	0.01240418	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	44.0	3.73245E-5	mg	
Material	2	Tin Plate				44.0	0.0902773	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	44.0	9.018702E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	44.0	0.09018711	mg	
Material	2	Phos Bronze				44.0	30.25	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	44.0	28.64176	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	44.0	0.00605	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	44.0	0.003025	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	44.0	1.36125	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	44.0	0.0045375	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	44.0	0.03025	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	44.0	0.003025	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	44.0	3.025E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	44.0	0.09075	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	44.0	0.03025	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	44.0	0.03025	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	44.0	0.003025	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	44.0	0.015125	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	44.0	0.03025	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	44.0	1.5125E-4	mg	
Sub-Item	1	1645361-4				110.0	28.6372	mg	

Material	2	Nickel Plate				110.0	0.27	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	110.0	5.4E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	110.0	2.7E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	110.0	0.26919	mg	
Material	2	Palladium-Nickel Plate				110.0	0.0171	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	110.0	0.01368	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	110.0	0.00342	mg	
Material	2	Gold Plate				110.0	0.0098	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	110.0	0.0097706	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	110.0	2.94E-5	mg	
Material	2	Tin Plate				110.0	0.0903	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	110.0	9.02097E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	110.0	0.09020979	mg	
Material	2	Phos Bronze				110.0	28.25	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	110.0	26.74809	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	110.0	0.00565	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	110.0	0.002825	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	110.0	1.27125	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	110.0	0.0042375	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	110.0	0.02825	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	110.0	0.002825	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	110.0	2.825E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	110.0	0.08475	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	110.0	0.02825	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	110.0	0.02825	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	110.0	0.002825	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	110.0	0.014125	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	110.0	0.02825	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	110.0	1.4125E-4	mg	
Sub-Item	1	646337-2				1.0	3519.0	mg	
Material	2	PBT-GF20				1.0	3519.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	56.5	1.0	1988.235	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	105.57	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	703.8	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	175.95	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	17.595	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromophenyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	15.0	1.0	527.85	mg	