



Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A							
Supplier Information														
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	PROD COMPLIANCE ENGINEER							
Company Unique ID	-	Response Date	2013-07-02	Contact Email	cc.wu@te.com									
Contact Phone Number	(86)21-33259321													
Legal Statement														
Supplier Acceptance	true													
Legal Statement														
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.														
Product														
Manufacturer Item number	640445-2	Amount	565.5259401	Version	-	Identity								
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority								
Date		UOM	Each											
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions													
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products													
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH													
Product Disclosure														
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption					
Sub-Item	1	702429-9				1.0	203.6259401	mg						
Material	2	Brass				1.0	202.3863655	mg						
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	144.70625	mg						
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00202386	mg						
Substance	3	Zinc	Supplier	7440-66-6	27.9975	1.0	56.66312	mg						
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.10119	mg						
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00202386	mg						
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.10119	mg						
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.20239	mg						
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.02023864	mg						
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.02023864	mg						
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.14167	mg						
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.02023864	mg						
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00101193	mg						
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.40477	mg						
Material	2	Tin Plate				1.0	0.769791	mg						
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	7.6902E-4	mg						
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.76902	mg						
Material	2	Nickel Plate				1.0	0.4697836	mg						
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	9.3957E-4	mg						
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	4.6978E-4	mg						
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.46837	mg						
Sub-Item	1	Polyester Resin				1.0	361.9	mg						
Material	2	PBT-GF7				1.0	361.9	mg						
Substance	3	Phenol, 4,4'-(1-methylethylidene)bis-	Supplier	80-05-7	0.01	1.0	0.03619	mg						
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	6.5	1.0	23.5235	mg						

Substance	3	Carbonic dichloride, polymer with 4,4'-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4'-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	108.57	mg	
Substance	3	Antimony oxide (Sb ₂ O ₃)	Supplier	1309-64-4	8.0	1.0	28.952	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	3.619	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.49	1.0	197.19931	mg	