



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance																											
Company Unique ID	485203835	Response Date	2014-07-07	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	640456-3	Amount	588.57200036	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	640451-2				1.0	329.0	mg																										
Material	2	PBT				1.0	329.0	mg																										
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	0.658	mg																										
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	16.45	mg																										
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	0.329	mg																										
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	26.32	mg																										
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	1.0	0.329	mg																										
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	1.645	mg																										
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	1.0	0.329	mg																										
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	98.7	mg																										
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	1.0	1.645	mg																										

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	1.0	16.45	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	1.0	6.58	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	1.0	0.329	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	1.0	159.236	mg	
Sub-Item	1	3-702429-2				3.0	86.52400012	mg	
Material	2	Brass Wire				3.0	84.0	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	0.0588	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	60.06	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	8.4E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	3.0	23.5179	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.042	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	8.4E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.042	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.084	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.0084	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.0084	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.0084	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	4.2E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.168	mg	
Material	2	Tin Plate				3.0	1.794	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	3.0	0.00179221	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	3.0	1.79221	mg	
Material	2	Nickel Plate				3.0	0.73	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.00146	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	7.3E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.72781	mg	