



| | | | | | | | | | |
|---|--|---|---------------------------|----------------------|--------------------------------|----------------------|-----------------------------|----------------------|------------------|
| Form Type | Distribute | Version | 2.0 | Ref | IPC 1752A | Sectionals | Material Info | Subsectionals | D, A |
| Supplier Information | | | | | | | | | |
| Company Name | TE Connectivity | Request Document ID | | Contact Name | David Benfer | Contact Title | Product Compliance Engineer | | |
| Company Unique ID | 485203835 | Response Date | 2014-04-22 | Contact Email | dave.benfer@te.com | | | | |
| Contact Phone Number | 717-986-3725 | | | | | | | | |
| Legal Statement | | | | | | | | | |
| Supplier Acceptance | true | | | | | | | | |
| Legal Statement | | | | | | | | | |
| The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers. | | | | | | | | | |
| Product | | | | | | | | | |
| Manufacturer Item number | 535097-5 | Amount | 15172.1284 | Version | - | Identity | | | |
| Manufacturer Item Name | | Weight Uom | mg | Mfr Site | | Authority | | | |
| Date | | UOM | Each | | | | | | |
| EUroHS-0508 | Product(s) does not meet EU RoHS requirements and is not under exemptions - true | | | | | | | | |
| ChinaRoHS-0508 | Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true | | | | | | | | |
| Product Disclosure | | | | | | | | | |
| Sub-Item/Material/Substance | Level | Name | Substance Category | Substance CAS | Substance Concentration | Quantity | Mass per Unit | UOM | Exemption |
| Sub-Item | 1 | 535041-1 | | | | 1.0 | 9776.8 | mg | |
| Material | 2 | Polyester Compound | | | | 1.0 | 9776.8 | mg | |
| Substance | 3 | Glass, oxide, chemicals | Supplier | 65997-17-3 | 32.0 | 1.0 | 3128.576 | mg | |
| Substance | 3 | Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17) | Supplier | 1043-4-FR17 | 12.0 | 1.0 | 1173.216 | mg | |
| Substance | 3 | 1,4-Benzenedicarb oxyclic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol | Supplier | 30965-26-5 | 47.0 | 1.0 | 4595.096 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0506 | 7.0 | 1.0 | 684.376 | mg | |
| Substance | 3 | Antimony oxide (Sb2O3) | Supplier | 1309-64-4 | 2.0 | 1.0 | 195.536 | mg | |
| Sub-Item | 1 | 535037-2 | | | | 120.0 | 44.96107 | mg | |
| Material | 2 | Phos Bronze | | | | 120.0 | 44.1 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 94.6835 | 120.0 | 41.75542 | mg | |
| Substance | 3 | Manganese | Supplier | 7439-96-5 | 0.02 | 120.0 | 0.00882 | mg | |
| Substance | 3 | Chromium | Supplier | 7440-47-3 | 0.01 | 120.0 | 0.00441 | mg | |
| Substance | 3 | Tin | Supplier | 7440-31-5 | 4.5 | 120.0 | 1.9845 | mg | |
| Substance | 3 | Arsenic | Supplier | 7440-38-2 | 0.015 | 120.0 | 0.006615 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 120.0 | 0.00441 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.1 | 120.0 | 0.0441 | mg | |
| Substance | 3 | Beryllium | Supplier | 7440-41-7 | 0.0010 | 120.0 | 4.41E-4 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 0.3 | 120.0 | 0.1323 | mg | |
| Substance | 3 | Phosphorus | Supplier | 7723-14-0 | 0.1 | 120.0 | 0.0441 | mg | |
| Substance | 3 | Cobalt | Supplier | 7440-48-4 | 0.1 | 120.0 | 0.0441 | mg | |
| Substance | 3 | Cadmium | Cadmium/Cadmium Compounds | 7440-43-9 | 0.01 | 120.0 | 0.00441 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.05 | 120.0 | 0.02205 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 0.1 | 120.0 | 0.0441 | mg | |
| Substance | 3 | Mercury | Mercury/Mercury Compounds | 7439-97-6 | 5.0E-4 | 120.0 | 2.205E-4 | mg | |
| Material | 2 | Tin-Lead Plate | | | | 120.0 | 0.1788 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 7.0 | 120.0 | 0.012516 | mg | |

| | | | | | | | | | |
|-----------|---|--|---------------------|---------------|------|-------|------------|----|--|
| Substance | 3 | Tin | Supplier | 7440-31-5 | 92.3 | 120.0 | 0.16503 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 0.7 | 120.0 | 0.0012516 | mg | |
| Material | 2 | Gold Plate | | | | 120.0 | 0.0146 | mg | |
| Substance | 3 | Gold | Supplier | 7440-57-5 | 99.7 | 120.0 | 0.0145562 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0909 | 0.3 | 120.0 | 4.38E-5 | mg | |
| Material | 2 | Nickel Plate | | | | 120.0 | 0.66767 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 0.2 | 120.0 | 0.00133534 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.1 | 120.0 | 6.6767E-4 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 99.7 | 120.0 | 0.66567 | mg | |