



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	485203835	Response Date	2014-07-03	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5352068-1	Amount	13605.859	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	9-5338107-2				1.0	3180.879	mg	
Material	2	Phos Bronze				1.0	3172.0	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	3003.36062	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.6344	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.3172	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	142.74	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.4758	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.3172	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	3.172	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.03172	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	9.516	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	3.172	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.172	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.3172	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.586	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	3.172	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01586	mg	
Material	2	Nickel Plate				1.0	7.995	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.01599	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.007995	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	7.97102	mg	
Material	2	Gold Plate				1.0	0.416	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.41475	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.001248	mg	
Material	2	Tin Plate				1.0	0.468	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	4.6753E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.46753	mg	
Sub-Item	1	994433-3				1.0	0.08	mg	
Material	2	444PC DOUBLE COATED TAPE				1.0	0.08	mg	

Substance	3	Poly(oxy-1,2-ethanedioxy carbonyl-1,4-phenylene carbonyl)	Supplier	25038-59-9	15.0	1.0	0.012	mg	
Substance	3	Resin acids and Rosin acids, hydrogenated, esters with glycerol	Supplier	65997-13-9	35.0	1.0	0.028	mg	
Substance	3	2-Propenoic acid, polymer with isooctyl 2-propenoate	Supplier	9017-68-9	50.0	1.0	0.04	mg	
Sub-Item	1	5352086-1				1.0	10424.9	mg	
Material	2	(PBT+PC)-(GF15+MD10)				1.0	4090.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	204.5	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	50.0	1.0	2045.0	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	5.0	1.0	204.5	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	818.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	10.0	1.0	409.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	10.0	1.0	409.0	mg	
Material	2	Phos Bronze				1.0	3097.6	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	2932.9161	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.61952	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.30976	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	139.392	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.46464	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.30976	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	3.0976	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.030976	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	9.2928	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	3.0976	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.0976	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.30976	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.5488	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	3.0976	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.015488	mg	
Material	2	Nickel Plate				1.0	51.7	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.1034	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0517	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	51.5449	mg	
Material	2	Gold Plate				1.0	5.72	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	5.70284	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.01716	mg	
Material	2	PBT-GF20				1.0	3168.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	62.79	1.0	1989.1872	mg	

Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	3.168	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	1.2	1.0	38.016	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.5	1.0	142.56	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.31	1.0	9.8208	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.1	1.0	3.168	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	633.6	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol], bis(2,4,6-tribromophenyl) ester	Brominated Flame Retardants (other than PBBs or PBDEs)	71342-77-3	11.0	1.0	348.48	mg	
Material	2	Tin Plate				1.0	11.88	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.01186812	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	11.86813	mg	