



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Product Compliance Engineer		
Company Unique ID	485203835	Response Date	2014-07-21	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5555164-1	Amount	2200.7876	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1-557500-5				1.0	390.7876	mg	
Material	2	Tin Plate				1.0	2.714	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00271129	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	2.71129	mg	
Material	2	Phos Bronze				1.0	385.2	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.3852	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.03852	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.7704	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.05778	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0335	1.0	346.80904	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.3482	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.07704	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.003852	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.03852	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.3852	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	34.668	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.3852	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.001926	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.03852	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.1926	mg	
Material	2	Nickel Plate				1.0	2.7858	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0027858	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0055716	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.77744	mg	
Material	2	Gold Plate				1.0	0.0878	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	2.634E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.0875366	mg	
Sub-Item	1	1-555076-1				1.0	1810.0	mg	
Material	2	PBT-GF20-FR(17)				1.0	1810.0	mg	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	1.81	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	5.43	mg	
Substance	3	Phosphoric acid, zinc salt (2:1)	Supplier	13598-37-3	1.0	1.0	18.1	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	36.2	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	20.0	1.0	362.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	362.0	mg	
Substance	3	Any substance originating from animal tissues of bovine, ovine, caprine, deer, elk, mink and cats species	Supplier	TE-Animal byproduct	1.0	1.0	18.1	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	181.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	44.6	1.0	807.26	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	18.1	mg	