



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER																											
Company Unique ID	485203835	Response Date	2014-04-14	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	66570-3	Amount	92.7036933	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	66570-2				1.0	92.7036933	mg																										
Material	2	Nickel Plate				1.0	2.190131	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.00438026	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00219013	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.18356	mg																										
Material	2	Gold Plate				1.0	0.1135623	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.11322	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	3.4069E-4	mg																										
Material	2	Brass				1.0	90.4	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	9.04E-4	mg																										
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	25.33234	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.0452	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00904	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.0452	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0904	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	9.04E-4	mg																										
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	64.636	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.00904	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.52E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.1808	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00452	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0452	mg																										