



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Mgr. Global Product Compliance		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2014-05-05	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	66602-8	<b>Amount</b>	608.02	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	788083-1				1.0	42.31	mg	
Material	2	Stainless Steel				1.0	42.31	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.004231	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.35	1.0	0.14808	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.231E-4	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.0	1.0	0.4231	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	1.0	0.8462	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.05	1.0	0.021155	mg	
Substance	3	Chromium	Supplier	7440-47-3	19.0	1.0	8.0389	mg	
Substance	3	Iron	Supplier	7439-89-6	66.4885	1.0	28.13128	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	1.0	0.063465	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.8	1.0	0.33848	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	1.0	0.012693	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.004231	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.004231	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.1155E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.0	1.0	4.231	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.04231	mg	
Sub-Item	1	1-66599-1				1.0	565.71	mg	
Material	2	Brass				1.0	547.74	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0054774	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	153.49044	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.27387	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.054774	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.27387	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.54774	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0054774	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	391.6341	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.054774	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0027387	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.09548	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.027387	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.27387	mg	
Material	2	Tin Plate				1.0	11.16	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.01114884	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	11.14885	mg	
Material	2	Nickel Plate				1.0	6.81	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.01362	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00681	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	6.78957	mg	