



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2013-12-20	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5650861-5	Amount	9252.1176	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1-535039-2				64.0	49.5034	mg	
Material	2	Phos Bronze				64.0	48.49	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	64.0	45.91203	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	64.0	0.009698	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	64.0	0.004849	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	64.0	2.18205	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	64.0	0.0072735	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	64.0	0.04849	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	64.0	0.004849	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	64.0	4.849E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	64.0	0.14547	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	64.0	0.04849	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	64.0	0.04849	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	64.0	0.004849	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	64.0	0.024245	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	64.0	0.04849	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	64.0	2.4245E-4	mg	
Material	2	Gold Plate				64.0	0.0146	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	64.0	0.0145562	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	64.0	4.38E-5	mg	
Material	2	Tin Plate				64.0	0.2593	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	64.0	2.5904E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	64.0	0.25904	mg	
Material	2	Palladium-Nickel Plate				64.0	0.0092	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	64.0	0.00736	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	64.0	0.00184	mg	
Material	2	Nickel Plate				64.0	0.7303	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	64.0	0.0014606	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	64.0	7.303E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	64.0	0.72811	mg	
Sub-Item	1	650490-6				1.0	6083.9	mg	

Material	2	PBT-GF20				1.0	6083.9	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	56.5	1.0	3437.4035	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	182.517	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	1216.78	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	304.195	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	30.4195	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromophenyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	15.0	1.0	912.585	mg	