



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	David Benfer	<b>Contact Title</b>	Product Compliance Engineer		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2014-04-22	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5745781-4	<b>Amount</b>	7568.687421	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	1761587-8				1.0	4852.207421	mg	
Material	2	PA66-GF25				1.0	3690.0	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	147.6	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	221.4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	129.15	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	61.5	1.0	2269.35	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	922.5	mg	
Material	2	Tin Plate				1.0	4.048225	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00404418	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	4.04418	mg	
Material	2	PA46-GF30				1.0	246.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.5	1.0	13.53	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.6	1.0	3.936	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.5	1.0	47.97	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0060	1.0	0.01476	mg	
Substance	3	Hexanedioic acid, polymer with 1,4-butanediamine	Supplier	50327-77-0	43.386	1.0	106.72956	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	73.8	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0080	1.0	0.01968	mg	
Material	2	Phos Bronze				1.0	900.3	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	852.43555	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.18006	mg	

Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.09003	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	40.5135	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.13505	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.09003	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.9003	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.009003	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	2.7009	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.9003	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.9003	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.09003	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.45015	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.9003	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0045015	mg	
Material	2	Nickel Plate				1.0	11.4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0228	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0114	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	11.3658	mg	
Material	2	Gold Plate				1.0	0.3274595	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.32648	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	9.8238E-4	mg	
Material	2	Gold Plate				1.0	0.1317365	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	3.9521E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.13134	mg	
Sub-Item	1	747331-3				2.0	154.74	mg	
Material	2	Brass				2.0	148.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.00148	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	41.4733	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.074	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0148	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.074	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.148	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00148	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	105.82	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0148	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	7.4E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.296	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.0074	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.074	mg	
Material	2	Copper Plate				2.0	3.71	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00371	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	2.0	3.70629	mg	
Material	2	Tin Plate				2.0	3.03	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	2.0	0.01212	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	2.0	3.01485	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00303	mg	
Sub-Item	1	749740-2				1.0	1829.0	mg	
Material	2	Carbon Steel				1.0	1829.0	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.4632	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.3658	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.3658	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1829	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.3658	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	2.7435	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.829	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.1829	mg	

Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	13.7175	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	7.316	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	1.829	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01829	mg	
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	1795.68477	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.9145	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.1829	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.009145	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.829	mg	
Sub-Item	1	5749017-1				2.0	289.0	mg	
Material	2	Zinc Alloy				2.0	289.0	mg	
Substance	3	Iron	Supplier	7439-89-6	0.08	2.0	0.2312	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	2.0	0.10115	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0289	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00289	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0020	2.0	0.00578	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	2.0	0.1445	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	2.0	0.0578	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	2.0	0.289	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.289	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.1445	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0289	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.2145	2.0	275.1699	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	2.0	12.427	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	2.0	0.0578	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0030	2.0	0.00867	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.001445	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0040	2.0	0.01156	mg	