



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Cc Wu	<b>Contact Title</b>	PROD COMPLIANCE ENGINEER		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2014-07-24	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	(86)21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	3-1571552-0	<b>Amount</b>	3161.87392	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>EUREACH-1213</b>	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	2-1437538-0				1.0	1048.0	mg	
Material	2	POLYESTER PCT				1.0	1048.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	9.75	1.0	102.18	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	28.5	1.0	298.68	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.0	1.0	199.12	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedi methanol	Supplier	25135-20-0	33.25	1.0	348.46	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	9.5	1.0	99.56	mg	
Sub-Item	1	1571580-2				32.0	66.05856	mg	
Material	2	Copper				32.0	32.0	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	32.0	0.0032	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	32.0	0.0064	mg	
Substance	3	Copper	Supplier	7440-50-8	99.6975	32.0	31.9032	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	32.0	3.2E-4	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	32.0	0.0032	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	32.0	3.2E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	32.0	0.032	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	32.0	0.0032	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	32.0	1.6E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	32.0	0.016	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	32.0	0.032	mg	
Material	2	Tin Plate				32.0	19.28	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	32.0	19.1836	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	32.0	0.07712	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	32.0	0.01928	mg	
Material	2	Gold Plate				32.0	0.00156	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	32.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	32.0	0.00155532	mg	
Material	2	Nickel Plate				32.0	9.277	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	32.0	0.018554	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	32.0	0.009277	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	32.0	9.24917	mg	
Material	2	Beryllium Copper				32.0	5.5	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	32.0	5.5E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.6	32.0	0.033	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	32.0	5.5E-5	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	32.0	0.11	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	32.0	0.0011	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	32.0	0.033	mg	
Substance	3	Copper	Supplier	7440-50-8	96.0485	32.0	5.28267	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	32.0	5.5E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.6	32.0	0.033	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	32.0	5.5E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	32.0	2.75E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	32.0	0.0055	mg	