



Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A		
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Vincent M Pascucci	Contact Title	Compliance Engineer		
Company Unique ID	-	Response Date	2013-03-07	Contact Email	vincent.pascucci@te.com				
Contact Phone Number	717-986-7822								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	87523-6	Amount	80.891	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Phos Bronze				1.0	79.217	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	0.079217	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.0079217	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.2	1.0	0.15843	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.015	1.0	0.01188255	mg	
Substance	2	Copper	Supplier	7440-50-8	90.0335	1.0	71.32184	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.35	1.0	0.27726	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	0.0158434	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	7.9217E-4	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.01	1.0	0.0079217	mg	
Substance	2	Iron	Supplier	7439-89-6	0.1	1.0	0.079217	mg	
Substance	2	Tin	Supplier	7440-31-5	9.0	1.0	7.12953	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.1	1.0	0.079217	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	3.9609E-4	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0079217	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0396085	mg	
Material	1	Tin Plate				1.0	1.674	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.35	1.0	0.005859	mg	
Substance	2	Tin	Supplier	7440-31-5	97.85	1.0	1.63801	mg	
Substance	2	Copper	Supplier	7440-50-8	1.5	1.0	0.02511	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.2	1.0	0.003348	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.001674	mg	