



Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A							
Supplier Information														
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Compliance Engineer							
Company Unique ID	TE Connectivity	Response Date	2013-06-25	Contact Email	dave.benfer@te.com									
Contact Phone Number	7179863725													
Legal Statement														
Supplier Acceptance	true													
Legal Statement														
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.														
Product														
Manufacturer Item number	640457-5	Amount	0.5384125	Version	-	Identity								
Manufacturer Item Name		Weight Uom	g	Mfr Site		Authority								
Date		UOM	Each											
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions													
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products													
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH													
Product Disclosure														
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption					
Sub-Item	1	3-702429-2				1.0	0.2810125	g						
Material	2	Nickel Plate				1.0	0.00228125	g						
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	4.5625E-6	g						
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.28125E-6	g						
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.00227441	g						
Material	2	Tin Plate				1.0	0.00560625	g						
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	5.600644E-6	g						
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.00560065	g						
Material	2	Brass				1.0	0.273125	g						
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	0.19528437	g						
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	2.73125E-6	g						
Substance	3	Zinc	Supplier	7440-66-6	27.9975	1.0	0.07646817	g						
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	1.3656E-4	g						
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	2.73125E-6	g						
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	1.3656E-4	g						
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.7312E-4	g						
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	2.73125E-5	g						
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	2.73125E-5	g						
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	1.9119E-4	g						
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	2.73125E-5	g						
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.365625E-6	g						
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	5.4625E-4	g						
Sub-Item	1	Polyester Resin				1.0	0.2574	g						
Material	2	PBT				1.0	0.2574	g						

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1'-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	5.148E-4	g	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	0.01287	g	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	2.574E-4	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	0.020592	g	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	1.0	2.574E-4	g	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	0.001287	g	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	1.0	2.574E-4	g	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	1.0	0.001287	g	
Substance	3	Carbonic dichloride, polymer with 4,4'-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4'-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	0.07722	g	
Substance	3	Carbonic dichloride, polymer with 4,4'-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	1.0	0.01287	g	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	1.0	0.005148	g	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	1.0	2.574E-4	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	1.0	0.1245816	g	