



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance																											
Company Unique ID	TE Connectivity	Response Date	2015-03-09	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1622548-1	Amount	205.48	Version	-	Identity																												
Manufacturer Item Name	LR1 1% 68K	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Epoxy resin(Color code)				1.0	1.0	mg																										
Substance	2	Oxirane, 2,2-[(1-methylethylidene)bis(4,1-phenyleneoxy methylene)]bis-, homopolymer	Supplier	25085-99-8	75.0	1.0	0.75	mg	N/A																									
Substance	2	copper phthalocyanine, chlorinated	Supplier	1328-53-5	25.0	1.0	0.25	mg	N/A																									
Material	1	PC-2				1.0	50.594	mg																										
Substance	2	Phenols (petroleum)	Supplier	64743-03-9	100.0	1.0	50.594	mg	N/A																									
Material	1	Iron alloy				1.0	14.59	mg																										
Substance	2	Iron	Supplier	7439-89-6	78.37	1.0	11.43418	mg	N/A																									
Substance	2	Tin	Supplier	7440-31-5	9.67	1.0	1.41085	mg	N/A																									
Substance	2	Copper	Supplier	7440-50-8	11.96	1.0	1.74496	mg	N/A																									
Material	1	Electrical ceramic				1.0	36.006	mg																										
Substance	2	Barium oxide (BaO)	Supplier	1304-28-5	5.88	1.0	2.11715	mg	N/A																									
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	72.55	1.0	26.12235	mg	N/A																									
Substance	2	Quartz (SiO2)	Supplier	14808-60-7	21.57	1.0	7.76649	mg	N/A																									
Material	1	Epoxy resin				1.0	10.9	mg																										
Substance	2	Carbonic acid calcium salt (1:1)	Supplier	471-34-1	3.03	1.0	0.33027	mg	N/A																									
Substance	2	Oxirane, 2,2-[(1-methylethylidene)bis(4,1-phenyleneoxy methylene)]bis-, homopolymer	Supplier	25085-99-8	70.0	1.0	7.63	mg	N/A																									
Substance	2	copper phthalocyanine, chlorinated	Supplier	1328-53-5	12.02	1.0	1.31018	mg	N/A																									
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	14.95	1.0	1.62955	mg	N/A																									
Material	1	Copper wire				1.0	91.8	mg																										
Substance	2	Copper	Supplier	7440-50-8	100.0	1.0	91.8	mg	N/A																									
Material	1	Resistor film				1.0	0.59	mg																										
Substance	2	Nickel	Nickel	7440-02-0	31.02	1.0	0.18302	mg	N/A																									
Substance	2	Chromium	Supplier	7440-47-3	56.95	1.0	0.336	mg	N/A																									

Substance	2	Aluminum	Supplier	7429-90-5	12.03	1.0	0.070977	mg	N/A
-----------	---	----------	----------	-----------	-------	-----	----------	----	-----