



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Mgr. Global Product Compliance		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2014-07-10	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	8-1437648-0	<b>Amount</b>	13475.08	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	8-1437649-0				6.0	1056.514	mg	
Material	2	Carbon Steel				6.0	839.179	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	6.0	0.33567	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.0839179	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	6.0	824.48078	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.0839179	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.83918	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	6.0	0.41959	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.00839179	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.23	6.0	1.93011	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	6.0	1.25877	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	6.0	8.39179	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.0839179	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	0.0041959	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.83918	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	6.0	0.41959	mg	
Material	2	Carbon Steel				6.0	217.3	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	6.0	0.32595	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.02173	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	6.0	0.10865	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.002173	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.9	6.0	1.9557	mg	
Substance	3	Iron	Supplier	7439-89-6	98.0285	6.0	213.01593	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	6.0	0.08692	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.02173	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.55	6.0	1.19515	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.2173	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	0.0010865	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.02173	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	6.0	0.10865	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.2173	mg	
Material	2	Tri Chrome Film				6.0	0.035	mg	

Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	6.0	0.021	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	6.0	0.0035	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	6.0	0.0105	mg	
Sub-Item	1	1437650-3				6.0	474.012	mg	
Material	2	Brass				6.0	464.096	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	0.00232048	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.4641	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	6.0	0.23205	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	6.0	0.00464096	mg	
Substance	3	Zinc	Supplier	7440-66-6	31.45	6.0	145.95819	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.00464096	mg	
Substance	3	Copper	Supplier	7440-50-8	68.0475	6.0	315.80573	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.0464096	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	6.0	0.23205	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.0464096	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.0464096	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	6.0	0.92819	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	6.0	0.32487	mg	
Material	2	Nickel Plate				6.0	2.318	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	0.004636	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.002318	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	2.31105	mg	
Material	2	Tin Plate				6.0	7.598	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	6.0	0.030392	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	6.0	7.56001	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.007598	mg	
Sub-Item	1	9-1437649-2				1.0	4291.924	mg	
Material	2	PA66				1.0	4291.924	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.3	1.0	12.87577	mg	
Substance	3	Nitrogen compounds - ISO 1043-4 code #FR(30)	Supplier	1043-4-FR30	8.0	1.0	343.35392	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	90.9	1.0	3901.35892	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.5	1.0	21.45962	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.3	1.0	12.87577	mg	