



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer																											
Company Unique ID	485203835	Response Date	2014-06-18	Contact Email	cc.wu@te.com																													
Contact Phone Number		+86-21-33259321																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	640551-3	Amount	321.45	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
EUREACH-0613	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	Polyester Compound				1.0	321.45	mg																										
Material	2	PBT				1.0	321.45	mg																										
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	0.6429	mg																										
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	16.0725	mg																										
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	0.32145	mg																										
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	25.716	mg																										
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	1.0	0.32145	mg																										
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	1.60725	mg																										
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	1.0	0.32145	mg																										
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	96.435	mg																										

Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	1.0	1.60725	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	1.0	16.0725	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	1.0	6.429	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	1.0	0.32145	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	1.0	155.5818	mg	