



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Cc Wu	<b>Contact Title</b>	PROD COMPLIANCE ENGINEER		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2014-05-06	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	(86)21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	643813-5	<b>Amount</b>	923.03	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) does not meet EU RoHS requirements and is not under exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	644817-5				1.0	459.5	mg	
Material	2	COLORANT				1.0	9.19	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	14.76	1.0	1.35644	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	1.0	1.0	0.0919	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediy)]	Supplier	25038-54-4	84.24	1.0	7.74166	mg	
Material	2	PA66				1.0	450.31	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	99.0	1.0	445.8069	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	4.5031	mg	
Sub-Item	1	640437-1				5.0	92.706	mg	
Material	2	Phos Bronze				5.0	90.4	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1335	5.0	84.19268	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	5.0	0.01808	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	5.0	0.2712	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	5.0	0.00904	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	5.0	0.3164	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	5.0	0.01356	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	5.0	0.0904	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	5.0	9.04E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	5.0	0.0904	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	5.0	0.00904	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	5.0	5.2432	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	5.0	4.52E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	5.0	0.00904	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	5.0	0.0452	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	5.0	0.0904	mg	
Material	2	Tin-Lead Plate				5.0	2.306	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	5.0	0.16142	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	5.0	2.12844	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	5.0	0.016142	mg	
-----------	---	--	----------	---------------	-----	-----	----------	----	--