



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china																											
Company Unique ID	TE Connectivity	Response Date	2015-04-01	Contact Email	cc.wu@te.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	34145	Amount	2209.424965	Version	-	Identity																												
Manufacturer Item Name	PG R 22-16 COMM 22-18 MIL 8	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	BUDG R 22-16 COMM 22-18 MIL 8				1.0	591.108965	mg																										
Material	2	Copper				1.0	586.3	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.29315	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.5863	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.005863	mg																										
Substance	3	Copper	Supplier	7440-50-8	99.6975	1.0	584.52644	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.005863	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.05863	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.05863	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.11726	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.5863	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0029315	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.05863	mg																										
Material	2	Tin Plate				1.0	4.808965	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	4.78492	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.01923586	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00480897	mg																										
Sub-Item	1	TUBING EXTRUDED				1.0	1618.316	mg																										
Material	2	PVC				1.0	1610.22442	mg																										
Substance	3	Ethene, chloro-	Supplier	75-01-4	2.0E-4	1.0	0.00322045	mg																										
Substance	3	Limestone	Supplier	1317-65-3	2.0	1.0	32.20449	mg																										
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	88.0	1.0	1416.99749	mg																										
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	1.5	1.0	24.15337	mg																										
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.1	1.0	1.61022	mg																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	8.3998	1.0	135.25563	mg	
Material	2	COLORANT				1.0	8.09158	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	70.0	1.0	5.66411	mg	
Substance	3	Glycerol	Supplier	56-81-5	0.01	1.0	8.0916E-4	mg	
Substance	3	Benzenesulfonic acid, 5-chloro-2-[2-(2-hydroxy-1-naphthalenyl)diazenyl]-4-methyl-, barium salt (2:1)	Supplier	5160-02-1	8.0	1.0	0.64733	mg	
Substance	3	Ethene, chloro-	Supplier	75-01-4	3.0E-4	1.0	2.427474E-5	mg	
Substance	3	Zeolites	Supplier	1318-02-1	0.19	1.0	0.015374	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4-[[2-[(2-ethylhexyl)oxy]-2-oxoethyl]thio]-4-methyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-34-3	0.8	1.0	0.06473264	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	0.8	1.0	0.06473264	mg	
Substance	3	Aluminum oxide (Al ₂ O ₃)	Supplier	1344-28-1	0.09	1.0	0.00728242	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	0.0809158	mg	
Substance	3	Aluminate (Al(OH) ₆ 3-), (OC-6-11)-, magnesium carbonate hydroxide (2:6:1:4)	Supplier	11097-59-9	0.7	1.0	0.05664106	mg	
Substance	3	Titanium oxide (TiO ₂)	Supplier	13463-67-7	8.0	1.0	0.64733	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	0.2	1.0	0.01618316	mg	
Substance	3	Silica	Supplier	7631-86-9	0.23	1.0	0.01861063	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	9.9797	1.0	0.80752	mg	