



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	JASON KUNTZ	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-04-13	Contact Email	jp.kuntz@te.com				
Contact Phone Number	717-986-5932								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	215307-2	Amount	1752.121	Version	-	Identity			
Manufacturer Item Name	2X2P HV100 REC CON. TE, 7.0MM	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	HV100 CNT U-ED, AU PLATED- NI UNDERPLATE				4.0	33.574	mg	
Material	2	Nickel Plate				4.0	0.048	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	9.6E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	4.8E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	0.047856	mg	
Material	2	Gold Plate				4.0	0.042	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	4.0	0.04158	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	4.0	4.2E-4	mg	
Material	2	Tin Plate				4.0	0.201	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	4.0	2.008E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	4.0	0.2008	mg	
Material	2	Gold Plate				4.0	0.0030	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	4.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	4.0	0.002991	mg	
Material	2	Phos Bronze				4.0	33.28	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	4.0	31.51067	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	0.006656	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	4.0	0.003328	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	4.0	1.4976	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	4.0	0.004992	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.003328	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	4.0	0.03328	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	3.328E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	4.0	0.09984	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	4.0	0.03328	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.03328	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	4.0	0.003328	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.01664	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	4.0	0.03328	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	1.664E-4	mg	
Sub-Item	1	2X36P HV100 HSG 7.0MM, TAPED				0.555	2915.0	mg	
Material	2	Polyester Compound				0.555	2915.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	50.0	0.555	1457.5	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	5.0	0.555	145.75	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	10.0	0.555	291.5	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	15.0	0.555	437.25	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	20.0	0.555	583.0	mg	