



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	485203835	Response Date	2014-03-19	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	747846-6	Amount	13862.116426	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions - true								
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	5749016-1				2.0	557.8857	mg	
Material	2	Tri Chrome Film				2.0	0.1857	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.05571	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	10.0	2.0	0.01857	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.11142	mg	
Material	2	Zinc Alloy				2.0	557.7	mg	
Substance	3	Iron	Supplier	7439-89-6	0.08	2.0	0.44616	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	2.0	0.1952	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.05577	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.005577	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0020	2.0	0.011154	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	2.0	0.27885	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	2.0	0.11154	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	2.0	0.5577	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.5577	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.27885	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.05577	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.2145	2.0	531.01127	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	2.0	23.9811	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	2.0	0.11154	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0030	2.0	0.016731	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.0027885	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0040	2.0	0.022308	mg	
Sub-Item	1	745798-2				1.0	537.0	mg	
Material	2	PA46-GF30				1.0	537.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.5	1.0	29.535	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.6	1.0	8.592	mg	

Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.5	1.0	104.715	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0060	1.0	0.03222	mg	
Substance	3	Hexanedioic acid, polymer with 1,4-butanediamine	Supplier	50327-77-0	43.386	1.0	232.98282	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	161.1	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0080	1.0	0.04296	mg	
Sub-Item	1	748663-2				2.0	127.7	mg	
Material	2	Brass				2.0	127.7	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.001277	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	35.78473	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.06385	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.01277	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.06385	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.1277	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.001277	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	91.3055	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.01277	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	6.385E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.2554	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.006385	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.06385	mg	
Sub-Item	1	747331-3				2.0	154.74	mg	
Material	2	Brass				2.0	148.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.00148	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	41.4733	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.074	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0148	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.074	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.148	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00148	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	105.82	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0148	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	7.4E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.296	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.0074	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.074	mg	
Material	2	Tin Plate				2.0	3.03	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	2.0	0.01212	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	2.0	3.01485	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00303	mg	
Material	2	Copper Plate				2.0	3.71	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00371	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	2.0	3.70629	mg	
Sub-Item	1	1-787661-4				13.0	110.5842002	mg	
Material	2	Phos Bronze				13.0	107.9	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	13.0	102.1635	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	13.0	0.02158	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	13.0	0.01079	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	13.0	4.8555	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	13.0	0.016185	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.01079	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	13.0	0.1079	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	0.001079	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	13.0	0.3237	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	13.0	0.1079	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.1079	mg	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	13.0	0.01079	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.05395	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	13.0	0.1079	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	5.395E-4	mg	
Material	2	Nickel Plate				13.0	2.28	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	13.0	0.00456	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	0.00228	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	2.27316	mg	
Material	2	Gold Plate				13.0	0.0150556	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.01501043	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	13.0	4.51668E-5	mg	
Material	2	Tin-Lead Plate				13.0	0.35	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	13.0	0.0245	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	13.0	0.32305	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	13.0	0.00245	mg	
Material	2	Gold Plate				13.0	0.0391446	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.03902717	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	13.0	1.1743E-4	mg	
Sub-Item	1	745788-2				1.0	5063.4	mg	
Material	2	PA66-GF25				1.0	5063.4	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	202.536	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	303.804	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	177.219	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	61.5	1.0	3113.991	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	1265.85	mg	
Sub-Item	1	1-787661-3				12.0	92.5642002	mg	
Material	2	Phos Bronze				12.0	90.2	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	12.0	85.40452	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	12.0	0.01804	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	12.0	0.00902	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	12.0	4.059	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	12.0	0.01353	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	12.0	0.00902	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	12.0	0.0902	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	12.0	9.02E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	12.0	0.2706	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	12.0	0.0902	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	12.0	0.0902	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	12.0	0.00902	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	12.0	0.0451	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	12.0	0.0902	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	12.0	4.51E-4	mg	
Material	2	Nickel Plate				12.0	1.96	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	12.0	0.00392	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	12.0	0.00196	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	12.0	1.95412	mg	
Material	2	Gold Plate				12.0	0.0150556	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	12.0	0.01501043	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	12.0	4.51668E-5	mg	
Material	2	Tin-Lead Plate				12.0	0.35	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	12.0	0.0245	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	12.0	0.32305	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.7	12.0	0.00245	mg	
Material	2	Gold Plate				12.0	0.0391446	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	12.0	0.03902717	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	12.0	1.1743E-4	mg	
Sub-Item	1	750176-2				1.0	4032.700021	mg	
Material	2	Carbon Steel				1.0	3948.9	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	3.15912	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.78978	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.78978	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.39489	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.78978	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	5.92335	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.9489	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.39489	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	29.61675	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	15.7956	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	3.9489	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.039489	mg	
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	3876.97079	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.97445	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.39489	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0197445	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.9489	mg	
Material	2	Tin Plate				1.0	52.062992	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.20825	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	51.80268	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.05206299	mg	
Material	2	Copper Plate				1.0	31.737029	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.03173703	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	31.70529	mg	